

Garant**SNMG 120408, Grade: HB7140-1**

Order data

Order number	251144 HB7140-1
GTIN	4045197820624
Item class	21G

Description

SNMG 120408 HB7140-1 Corner radius: 0.8 mm
Grade: HB7140-1
Chip breaker: VS
Cutting depth a_p : 0.3 - 2 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 260 m/min

Technical description

Feed f	0.1 - 0.4 mm/rev.
Grade	HB7140-1
Chip breaker	VS
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Cutting speed v_c main application	70 - 260 m/min
Cutting depth a_p	0.3 - 2 mm

Main application	M
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning