



## Forked clamp offset, Slot width a: 18mm



### Order data

Order number	370810 18
GTIN	4020772073251
Item class	35A

### Description

**Version:**

Quenched and tempered steel, painted.

**Application:**

To achieve the **lowest clamping height, turn the clamp around.**

**Material:**

Screw strength 8.8.

**Supplied with:**

Adjusting screw and T-bolts DIN 787 (see No. 375300).

### Technical description

Distance e from tip to end of slot	110 mm
Tee bolt DIN 787, No. 375300	Size 1816125
Slot width a	18 mm
Clamping height h	13 - 56 mm
Length L	160 mm

Height H	30 mm
Width B	50 mm
Type	6315V
Type of product	Plain clamp

---

## Accessories

Detent clamp lever Slot width a 16 mm	370750 16
---------------------------------------	-----------