

Morse taper clamping sleeve for taps, MT/Ø: 3/10**Order data**

Order number	345000 3/10
GTIN	4045197311740
Item class	37E

Description**Version:**

Through hardened, bore and external taper ground.

Application:

For mounting parallel shank taps and reamers with square drive.

Standard:

DIN 6328

Cutting data:

For fitting into adjustable adapters angle heads, quick-change tapping collets, and multi-spindle machines where the spindles are close together.

Note:

Not suitable for milling work!

for shank Ø: 10 mm

for shank □: 8 mm

Technical description

for shank Ø	10 mm
for shank □	8 mm
Type of product	Clamping sleeve