

Garant**WNMG 080412, Grade: HB7120-1**

Order data

Order number	252072 HB7120-1
GTIN	4045197820198
Item class	21G

Description

WNMG 080412 HB7120-1 Grade: HB7120-1
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting conditions	continuous
Corner radius	1.2 mm
Chip breaker	VM
Main application	M
Cutting speed v_c main application	80 - 260 m/min
Cutting depth a_p	0.5 - 4 mm
Grade	HB7120-1

Feed f	0.1 - 0.5 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080412
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning