



Magnetic measuring stand with fine adjustment at the column, Type: N2



Order data

Order number	441190 N2
GTIN	7290005395055
Item class	46G

Description

Version:

3-point clamping of the measuring arm with very short clamping travel for high ease of use. Very low applied force generates sustained stable clamping.

Generously dimensioned frame for very high system stiffness. **Vario** dial indicator holder for shank \varnothing 6mm, 8mm, 3/8 inch, lever dial indicator with dovetail slide and dial indicators with loop at rear.

Fine adjustment at the indicator holder.

Optional extras:

Measuring microscope No. 440401.

Technical description

Connection thread	M8 external thread
Column \varnothing D ₂	16 mm
Magnetic base height	55 mm
Cross arm length L ₁	225 mm

Magnetic force	1000 N
Magnetic base length	75 mm
Magnetic base width	50 mm
Column height L ₂	260 mm
Cross arm Ø D ₁	16 mm
Type of product	measuring stand

Accessories

Arm clamp for universal measuring stands for column Ø of stand 16/16 mm	440351 16/16
Stand base Type 0	442120 0
Stand base Type 1	442140 1
Stand base Type 0	442140 0
Vario dial indicator holder Type FA1500	440401 FA1500
Stand base Type 1	442120 1
Stand base Type V	442120 V
Stand base with fine adjustment Type 0	442125 0