



Magnetic measuring stand with fine adjustment at the column, Type: 600



Order data

Order number	441150 600
GTIN	7290005395130
Item class	46G

Description

Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Universal indicator holder with fine adjustment, for clamping shank \varnothing 8 mm, \varnothing 6 mm, \varnothing 3/8 inch and indicators with dovetail clamping shanks.

Callout:

Fine adjustment at the indicator holder

Technical description

Magnetic base width	50 mm
Length of jointed arm L_2	223 mm
Magnetic base length	120 mm
Magnetic force	1300 N
Magnetic base height	55 mm

Length of jointed arm L ₁	287 mm
Throat	580 mm
maximum loading	14 kg
Connection thread at bottom	M10×1.25
Type of product	measuring stand

Accessories

Stand base Type 2	442120 2
Stand base Type 2	442140 2
Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type K2	442100 K2
Stand base Type F	442120 F
Holder for measuring stand Type QR	442100 QR
Stand base with hydraulic fine adjustment Type 2	440865 2
Holder for measuring stand Type CA	442100 CA
3-D jointed arm Type 600	442114 600
3-D jointed arm Type 600	442110 600
Stand base Type 2	440868 2
Holder for measuring stand Type 2SM	442104 2SM
Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type H	442100 H