



## Measuring stand with fine adjustment at the magnetic base, Type: N0



### Order data

Order number	441195 N0
GTIN	7290005397318
Item class	46G

### Description

#### Version:

3-point clamping of the measuring arm with very short clamping travel for high ease of use. Very low applied force generates sustained stable clamping.

Generously dimensioned frame for very high system stiffness. **Vario** dial indicator holder for shank Ø 6mm, 8mm, 3/8 inch, lever dial indicator with dovetail slide and dial indicators with loop at rear.

**Fine adjustment at the magnetic base.** Advantage when adjusting µm lever dial indicators, as the column is not affected by the force applied.

#### Optional extras:

Measuring microscope No. 440401.

### Technical description

Column Ø D <sub>2</sub>	10 mm
Column height L <sub>2</sub>	120 mm
Magnetic base length	40 mm
Magnetic base height	35 mm

Magnetic force	320 N
Magnetic base width	30 mm
Cross arm length L <sub>1</sub>	110 mm
Cross arm Ø D <sub>1</sub>	8 mm
Connection thread	M5 external thread
Type of product	measuring stand

---

## Accessories

Vario dial indicator holder Type FA1210	440401 FA1210
Arm clamp for universal measuring stands for column Ø of stand 10/8 mm	440351 10/8
Stand base Type S	442140 S
Stand base Type S	442120 S
Stand base with fine adjustment Type S	442125 S