

**Digital workshop caliper, Measuring range: 300mm****Order data**

Order number	415528 300
GTIN	4045197492494
Item class	42A

Description**Version:**

Easy-to-read display. Optimum guidance and sliding characteristics due to **double Vee guides**. Stainless steel jaws, precision ground. The left-hand measurement jaw is moveable.

Supplied with:

Manufacturer's test certificate. Up to size 1000 including plastic wallet, from size 1500 sturdy transport packaging.

1 battery No. 081560 size LR44.

Technical description

Internal jaw Ø	10 mm
Weight	0.5 kg
Measuring range	0 - 300 mm
Jaw length	90 mm
Calibration	A1
Scale divisions	0.01 mm
Error limit	0.04 mm
#Article no of the battery / rechargeable battery fitted	081560 LR44
#Number of batteries contained	1
Power supply	Battery-powered

Standard	Works standard
Measurement technology	digital
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/415528-300>