

Garant**VNMG 160408, Grade: HB7120-1**

Order data

Order number	251804 HB7120-1
GTIN	4045197820105
Item class	21G

Description

VN.G 160408 HB7120-1 Grade: HB7120-1
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 80 - 260 m/min

Technical description

Feed f	0.1 - 0.5 mm/rev.
Main application	M
Corner radius	0.8 mm
Grade	HB7120-1
Chip breaker	VM
Cutting conditions	continuous

Cutting speed v_c main application	80 - 260 m/min
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning