


**Garant**
**SNMG 120408, Grade: HB7415**


### Order data

Order number	251144 HB7415
GTIN	4045197816573
Item class	21G

### Description

SNMG 120408 HB7415 Corner radius: 0.8 mm  
 Grade: HB7415  
 Chip breaker: TIS  
 Cutting depth  $a_p$ : 0.3 - 2 mm  
 Feed  $f$ : 0.1 - 0.2 mm/rev.  
 Cutting speed  $v_c$  main application: 60 - 70 m/min

### Technical description

Main application	S
Corner radius	0.8 mm
Cutting speed $v_c$ main application	60 - 70 m/min
Chip breaker	TIS
Grade	HB7415
Feed $f$	0.1 - 0.2 mm/rev.
Cutting conditions	continuous

Cutting depth $a_p$	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Type of product	Indexable insert for turning