



DS double-ended grinding machine, 400 V, Type: DS04/175



Order data

Order number	077512 DS04/175
GTIN	2050001674173
Item class	03S

Description

Version:

The **extremely smooth-running** motor ensures a long working life, even when run **continuously. Supplied without grinding wheels.**

Exceptionally robust three-phase double-ended bench grinding machines, bench-top type. Sturdy workpiece supports, restart inhibit, and eye protection shields ensure user safety.

Note:

Suitable grinding wheels can be found from No. 596100.

Technical description

Power consumption	250 W
Weight	15 kg
Manufacturer's designation	DS04/175
maximum speed	2900 min ⁻¹
Abrasive disc width T	25 mm
Abrasive disc hole Ø H	51 mm
Abrasive disc Ø D	175 mm
Power supply	Mains operated
Type of product	Double grinding machine

Accessories

Bench grinding wheel D×T×H (mm) Type SC80	596350 SC80
Support stand suitable for machine DS04	077513 DS04
Bench grinding wheel D×T×H (mm) Type EK60	596220 EK60
Bench grinding wheel D×T×H (mm) Type C800	596350 C800
Bench grinding wheel D×T×H (mm) Type EK60	596350 EK60
Bench grinding wheel D×T×H (mm) Type NK36	596350 NK36
Tool mounting plate right-hand Type AT1	077525 AT1
Bench grinding wheel D×T×H (mm) Type NK60	596350 NK60
Bench grinding wheel D×T×H (mm) Type NK60	596220 NK60
Bench grinding wheel D×T×H (mm) Type SC80	596220 SC80
Bench grinding wheel D×T×H (mm) Type EK80	596220 EK80
Tool mounting plate left-hand Type AT1	077519 AT1
Bench grinding wheel D×T×H (mm) Type EK80	596350 EK80