



Short drill chuck Form A, BT 40, Clamping range: 2,5-16mm



Order data

Order number	303197 2,5-16
GTIN	2050001701268
Item class	33W

Description

Version:

For clockwise and anticlockwise rotation.

Supplied with:

Clamping wrench.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	2.5 - 16 mm
Overhang dimension A	103 mm
Spare chuck key No. 627425	6 AF
External Ø D	57 mm
Adapter	BT 40
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

Accessories

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40