



## Wedge block "Herkules", highest support height: 125mm



### Order data

Order number	374900 125
GTIN	4020772072780
Item class	35A

### Description

#### Version:

Very rigid design; spheroidal graphite cast iron and hardened steel. **The ground wedge surfaces provide for precision and even height adjustment** with an accuracy better than 0.1mm. Either the knurled screw or a hexagon socket wrench can be used for height adjustment. The double action results in a long stroke and precise vertical movement without lateral displacement.

#### Application:

**Particularly for working with heavy cast or forged parts** on large machine tools after marking-out.

#### Supplied with:

**Interchangeable ball jack pad No. 375000.**

#### Note:

Flat component support face with centring hole  $\varnothing$  12 mm for jack pads No. 375000 – 375030.

### Technical description

Load capacity	100 kN
Footprint length	125 mm
lowest support height	100 mm

Footprint width	115 mm
highest support height	125 mm
Height adjustment per spindle rotation	1.16 mm
Type	6460
Type of product	Wedge