



Flat clamp, Slot width a: 16mm



Order data

Order number	375115 16
GTIN	4020772374167
Item class	35A

Description

Version:

Low design, position the flat clamp on the workpiece. Then tighten the securing screws for the machine table. The workpiece is clamped by turning the clamping screw.

Application:

For lateral clamping of especially thin components, in order to perform complete machining operations without interference contours. Can be used both horizontally and vertically.

Material:

Hardened steel, burnished finish.

Technical description

Maximum height h_2	25 mm
Minimum height h_1	16 mm
Clamping force F_1 horizontal	15 kN
Thread G	M12
Intermediate height H_1	16 mm
Clamping force F_2 vertical	7.5 kN
Slot width a	16 mm
Length L	110 mm
Width B	44 mm

Type	6496
Type of product	Side clamps