



Flat clamp, Slot width a: 18mm



Order data

Order number	375115 18
GTIN	4020772374174
Item class	35A

Description

Version:

Low design, position the flat clamp on the workpiece. Then tighten the securing screws for the machine table. The workpiece is clamped by turning the clamping screw.

Application:

For lateral clamping of especially thin components, in order to perform complete machining operations without interference contours. Can be used both horizontally and vertically.

Material:

Hardened steel, burnished finish.

Technical description

Thread G	M16
Clamping force F_2 vertical	12.5 kN
Clamping force F_1 horizontal	25 kN
Minimum height h_1	19 mm
Maximum height h_2	30 mm
Intermediate height H_1	19 mm
Slot width a	18 mm
Length L	130 mm
Width B	56 mm

Type	6496
Type of product	Side clamps