

**PLANOLITH**
**Universal precision comparator stand with 3-D NOGA jointed arm, Table length×Width: 400X400mm**

**Order data**

Order number	442525 400X400
GTIN	2050001052469
Item class	46H

**Description**
**Version:**

Precision diamond lapped table, with test certificate. Solid 3D jointed arm with mechanical central clamping. Continuously adjustable clamping force with high stability. Quick and easy positioning. Universal indicator holder.

With fine adjustment, for clamping shank  $\varnothing$  8 mm,  $\varnothing$  6 mm,  $\varnothing$  3/8 inch and indicators with dovetail clamping shanks.

**Technical description**

Weight	28 kg
Action radius of 3-D jointed arm	600 mm
Length of jointed arm $L_2$	223 mm
Connection thread	M10×1.25
Length of jointed arm $L_1$	287 mm
Standard	DIN 876/1

Test certificate	Manufacturer's test certificate
Calibration	D1
Type of product	Comparator stand

### Services

CalibrationComparator stand maximum table size 400X400 mm	024580 400X400
--	----------------

### Accessories

3-D jointed arm Type 600	442110 600
3-D jointed arm Type 600	442114 600
Holder for measuring stand Type 2SM	442100 2SM