



## Bench centre with ground measuring faces, without dial indicator, Tip height: 150mm



### Order data

Order number	443000 150
GTIN	4030234000305
Item class	46K

### Description

**Version:****Measuring stand:**

With fine setting adjustment and holder bore 8 H7. The cross arm is full adjustable for height and in all lateral directions.

**Tailstocks:**

adjustable. Left tailstock with fixed centre, right tailstock with axially movable quill.

**Measuring bench:**

Precision ground, with 2 T-slots. To take the tailstocks (tolerance H7) or the stand.

**Flatness to DIN 876/1.****Application:**

For measuring round and plane accuracy as well as for comparative tests of parallelism and diameter.

**Supplied with:**

Bench, measuring stand. Tailstocks without Vee blocks.

### Technical description

Centre $\emptyset$	22 mm
Footprint length	700 mm
Baseplate width	180 mm

Weight	38 kg
Lateral and vertical alignment of tailstocks	±0.01 mm
Column Ø	22 mm
Tip height	150 mm
Maximum clear span between centres	450 mm
Pillar height	250 mm
overall height without stand	250 mm
Cross arm length	125 mm
Cross arm Ø	16 mm
T-slot width H7	12 mm
Calibration	Price on request
maximum load capacity per pair	20 kg
Type of product	Radial and axial run-out tester

---

## Accessories

Pair of bench inspection rollers for tip height 100 mm	443160 100
Pair of bench inspection rollers height adjustable for maximum workpiece Ø 65 mm	443050 65