


**Bench centre RPG, for maximum workpiece Ø: 50mm****Order data**

Order number	443300 50
GTIN	2050001944733
Item class	46L

Description**Version:**

Robust design with pre-loaded roller bearings.

Type RPG for inspections in series production with 2 pivoting holders and 1 measuring slide (apart from size 30).

Application:

For inspection tasks on external, internal, and flat faces of rotating parts.

Accuracy:

Concentricity **0.002 mm.**

Supplied with:

Key and oilstone (without dial indicator).

Optional extras:

Cross slide for measurement of flat surfaces.

Measurement slide with centres or coated rollers.

Jointed arm with measuring tool mount.

Carbide-coated rollers.

Electrical drive with variable transformer.

Pneumatic pivoting arm with tensioning roller.

Note:

All types are available on request with a different type of roller (grooved rollers or cylindrical rollers).

Technical description

Footprint length	400 mm
------------------	--------

Roll Ø	50 mm
for workpiece Ø	4 - 50 mm
Baseplate width	160 mm
for maximum workpiece Ø	50 mm
Roller type	cylindrical rollers
Weight	11 kg
Type of product	Radial and axial run-out tester