

Mitutoyo
Digital external micrometer large, Measuring range: 150-300mm

Order data

| | |
|--------------|----------------|
| Order number | 421558 150-300 |
| GTIN | 4946368695891 |
| Item class | 44A |

Description
Version:

Hardened and ground measuring spindle and measuring faces; locked by locking lever. With ratchet. **6 easily interchangeable measuring anvils give a measuring range of 150 mm per set.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Accuracy:

$(4 + L / 75) \mu\text{m}$

Supplied with:

Measuring spindles, setting standards, 1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445.

Technical description

| | |
|--------------------------------|---------|
| Number of micrometer standards | 6 |
| Spindle pitch | 0.5 mm |
| Spindle travel | 25 mm |
| Spindle \emptyset | 6.35 mm |
| Barrel \emptyset | 18 mm |

| | |
|---|--------------------------|
| Measuring range | 150 - 300 mm |
| Weight | 1.88 kg |
| Scale divisions | 0.001 mm |
| Calibration | S3 |
| Article no of the battery / rechargeable battery fitted | 081560 357 |
| Number of batteries contained | 1 |
| IP Index of Protection | IP 65 |
| Power supply | Battery-powered |
| Standard | DIN 863 |
| Interface | USB interface |
| Interface | Digimatic interface |
| Measurement technology | digital |
| Packaging | sturdy box |
| Type of product | External tube micrometer |

Services

| | |
|--|----------------|
| Calibration External micrometers with extensions Measuring range 150-300 mm | 020450 150-300 |
|--|----------------|

Accessories

| | |
|--|-------------|
| Button cell / special battery Battery type 357 | 081560 357 |
| Connecting cable with data switch Type D2 | 497445 D2 |
| Connecting cable with data switch Type USB2 | 497445 USB2 |
| Connecting cable with data switch Type D1 | 497445 D1 |
| Transmitter Type S16E | 498966 S16E |
| Multi-receiver / USB keyboard interface Type | 498975 |
| Receiver / USB keyboard interface Type | 498965 |