

Hartig

**Precision external micrometer with 50 mm spindle travel, Measuring range: 50-100mm****Order data**

Order number	420900 50-100
GTIN	4250099609196
Item class	46P

**Description****Version:**

Stable spheroidal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863.

**Advantage:**

50 mm spindle travel, ideal for larger measurement ranges. Direct reading of the 1/100 mm on the large scale barrel.

**Supplied with:**

Without setting standard.

**Technical description**

Spindle Ø	8 mm
Measuring range	50 - 100 mm
Micrometer barrel graduations	1/100 mm
Scale divisions	0.01 mm
Barrel Ø	24 mm
Calibration	B1
Error limit	4 µm
Standard	Manufacturer's standard

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

### Services

Calibration External micrometer without setting dimension maximum measuring range 100 mm	022000 100
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100

### Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------