


**Garant**

**Die maker's square hardened stainless, accuracy class 00, Stock length:  
25X20mm**

**Order data**

Order number	450040 25X20
GTIN	4045197444035
Item class	41G

**Description****Version:**

Highest accuracy. Bevelled edge on long narrow blade. High-tensile steel, fully hardened and stress-relieved. Test faces ground and lapped. All other faces ground.

**Application:**

For jig and tool making.

**Technical description**

Length of short arm	20 mm
Length of long arm	25 mm
Right angle tolerance	0.003 mm
Cross-section of short arm	4x3.5 mm
Standard	DIN 875/00
Material	Stainless steel, INOX

all parts	hardened
Packaging	sturdy box
Calibration	F1
Type of product	Try squares

**Services**

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
---	------------