

**Mitutoyo****External micrometer with Vee-anvil, Measuring range: 5-25mm****Order data**

Order number	422300 5-25
GTIN	4946368010151
Item class	44A

**Description****Version:**

**With Vee anvil for measuring three or five-flute cutters.** Enamelled frame. Spindle pitch correction for Vee angle. **Pentagonal** with a Vee angle of 108°.

**Application:**

For measuring **3 or 5 flute cutters** (end mills, reamers).

**Supplied with:**

Setting standard.

**Technical description**

Vee angle	108 (pentagonal) degrees
Barrel Ø	18 mm
Measuring range	5 - 25 mm
Micrometer barrel graduations	1/50 mm
Spindle Ø	6.35 mm
Scale divisions	0.01 mm
Calibration	B8
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box

Type of product

External micrometer

---

**Services**

Calibration Thread flanks external micrometer including  
setting dimension maximum nominal size 100 mm

022320 100