

**Mitutoyo**
**Digital external micrometer with disc anvils, Measuring range: 25-50mm**

**Order data**

Order number	421660 25-50
GTIN	4946368689548
Item class	44A

**Description**
**Version:**

**Clear (7.5 mm high), digital measured value display provides quick readings. Addition reading by vernier.** Sintered, precision lapped, carbide tipped anvils, measuring spindle hardened and ground. Locking by clamping screw. Measuring force at the ratchet 5 - 10 N.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

From size 25-50 including 1 setting standard. 1 battery No. 081560 size 357.

**Optional extras:**

Data cable No. 497445.

**Technical description**

Measuring range	25 - 50 mm
Parallelism of the measuring faces	4 µm
Calibration	B2
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863

Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Type of product	External micrometer

## Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

## Accessories

Receiver / USB keyboard interface Type	498965
Micrometer setting standard overall length 25 mm	421100 25
Multi-receiver / USB keyboard interface Type	498975
Button cell / special battery Battery type 357	081560 357
Transmitter Type S16E	498966 S16E
Connecting cable with data switch Type D2	497445 D2
Connecting cable with data switch Type D1	497445 D1
Connecting cable with data switch Type USB2	497445 USB2