

**Stationary chuck MANOK, Clamping head (SK): 52****Order data**

Order number	329810 52
GTIN	2050001922489
Item class	33H

**Description****Version:**

Stationary chuck of solid cast. High clamping force, precision and rigidity.

**Application:**

Versatile application, e.g. machining centres, measuring machines, pillar drills.

**Supplied with:**

Including 1 chuck key.

**Note:**

For suitable clamping heads see No.329910–329946.

**Technical description**

Height H	124 mm
Width B	159 mm
Weight	14 kg
Length L	214 mm
Arbor size	52
Width across flats	17 mm
Spacing of attachment holes	184 mm

Repetition accuracy	0.01 mm
maximum clamping force	90 kN
Pitch circle Ø	120 mm
Head Ø	80 mm
Clamping range	4 - 52 mm
Type of product	Vice