

**Hartig****External thread micrometer without anvils, Measuring range: 50-75mm****Order data**

Order number	422340 50-75
GTIN	4250099618372
Item class	46P

**Description****Version:**

Hardened and ground measuring spindle with bore for the measuring tips. Glare-free satin chrome-plated barrel. With sensitive ratchet (friction lock) and quick drive for rapid adjustment. Heat-insulated frame.

**Application:**

**For practical measurement of flank  $\varnothing$  of external threads.** One pair of anvils (Vee and cone) fits several pitches, providing the flank angle remains unchanged.

**Supplied with:**

From size 25–50 with  $1 \times 60^\circ$  setting standard; without thread measurement inserts.

**Optional extras:**

Vee and cone anvils No. 421652.

**Note:**

Further measurement ranges available on request.

**Technical description**

Measuring range	50 - 75 mm
Spindle pitch	0.5 mm
Barrel $\varnothing$	20 mm
Spindle $\varnothing$	6.5 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm

Calibration	Price on request
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

## Accessories

Pair of anvils for external thread micrometers Pitch 3,5-5 mm	421652 3,5-5
Pair of anvils for external thread micrometers Pitch 0,6-0,9 mm	421652 0,6-0,9
Pair of anvils for external thread micrometers Pitch 1-1,75 mm	421652 1-1,75
Pair of anvils for external thread micrometers Pitch 5,5-7 mm	421652 5,5-7
Pair of anvils for external thread micrometers Pitch 0,4-0,5 mm	421652 0,4-0,5
Pair of anvils for external thread micrometers Pitch 2-3 mm	421652 2-3