



DS double-ended grinding machine, 400 V, Type: DS15/300



Order data

Order number	077512 DS15/300
GTIN	2050001673954
Item class	03S

Description

Version:

The **extremely smooth-running** motor ensures a long working life, even when run **continuously. Supplied without grinding wheels.**

Exceptionally robust three-phase double-ended bench grinding machines, bench-top type. Sturdy workpiece supports, restart inhibit, and eye protection shields ensure user safety.

Note:

Suitable grinding wheels can be found from No. 596100.

Technical description

Manufacturer's designation	DS15/300
Weight	80 kg
Power consumption	1100 W
maximum speed	1450 min ⁻¹
Abrasive disc width T	40 mm
Abrasive disc hole Ø H	76 mm
Abrasive disc Ø D	300 mm
Power supply	Mains operated
Type of product	Double grinding machine

Accessories

Eye protection shield for No. 077502 Type DS2	077509 DS2
Bench grinding wheel D×T×H (mm) Type NK60	596610 NK60
Tool mounting plate left-hand Type AT2	077519 AT2
Support stand suitable for machine DS15	077513 DS15
Bench grinding wheel D×T×H (mm) Type SC80	596610 SC80
Bench grinding wheel D×T×H (mm) Type EK60	596610 EK60
Tool mounting plate right-hand Type AT2	077525 AT2