

**Garant****Parallel clamping jaw, Jaw width: 80mm****Order data**

Order number	360085 80
GTIN	4045197482426
Item class	310

**Description****Application:**

Variable pitches can be achieved using crossed clamping rails.

**Suitable for:**

Clamping rail No. 360080.

**Note:**

For use with clamping rails from revision 3 onwards (see illustration). Attachment bar on multi-point clamping rails must not be wider than 5 mm.

**Technical description**

Jaw width	80 mm
Clamping force	5 kN
Clamping force	10 kN
Clamping force	15 kN
Clamping force	20 kN
Torque	5 Nm
Torque	10 Nm

Torque	15 Nm
Torque	20 Nm
max. stroke	3.5 mm
T-bolt AF	5 mm
Shank screw AF <sub>1</sub>	4 mm
Type of product	Vice jaws