


 Mahr**Indicating snap gauge, Measuring range: 0-25mm****Order data**

Order number	424900 0-25
GTIN	4059192017590
Item class	43A

Description**Version:**

Powerful, forged steel frame with thermal insulation. Anvils made of stainless, hardened steel. Anvil spring mounted, can be pulled back by a lever to insert the component. Anvil adjustable over the measuring range by rack and knurled screw. Setting by gauge blocks. Adjustable centring back-stop for setting component centre. **Constant gauging force** ensured by built-in gauging force spring. Can be used with all dial gauges (not included in the price) with 8 mm clamping shank. Precision dial comparators No. 434674 size 25/0.5 and size 50/1 are preferred.

Out-of-tolerance component values can be read numerically on the dial indicator.

With carbide-tipped measuring faces. For cylindrical parts such as shafts, bolts, and shanks, for measuring thickness and length.

Supplied with:

Without dial indicator, **with a** wooden box.

Optional extras:

Setting dimensions, precision dial comparator No. 434674. Cast micrometer stand, holder for dial comparator for straight-line transmission of the measurement movement, anvils.

Technical description

Measuring face \varnothing	8 mm
Gauging force	7.5 N

Measuring range	0 - 25 mm
Plane parallelism of measuring faces	1 μm
Contact point travel	2 mm
Flatness of measuring faces	0.2 μm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Calibration	L9
Type of product	Indicating snap gauge

Services

Calibration Adjustable snap gauge Type RL	028730 RL
---	-----------