




## Indicating snap gauge, Measuring range: 50-100mm



### Order data

Order number	424900 50-100
GTIN	4059192017613
Item class	43A

### Description

#### Version:

Powerful, forged steel frame with thermal insulation. Anvils made of stainless, hardened steel. Anvil spring mounted, can be pulled back by a lever to insert the component. Anvil adjustable over the measuring range by rack and knurled screw. Setting by gauge blocks. Adjustable centring back-stop for setting component centre. **Constant gauging force** ensured by built-in gauging force spring. Can be used with all dial gauges (not included in the price) with 8 mm clamping shank. Precision dial comparators No. 434674 size 25/0.5 and size 50/1 are preferred.

**Out-of-tolerance component values can be read numerically on the dial indicator.**

With carbide-tipped measuring faces. For cylindrical parts such as shafts, bolts, and shanks, for measuring thickness and length.

#### Supplied with:

**Without** dial indicator, **with a** wooden box.

#### Optional extras:

Setting dimensions, precision dial comparator No. 434674. Cast micrometer stand, holder for dial comparator for straight-line transmission of the measurement movement, anvils.

### Technical description

Plane parallelism of measuring faces	2 µm
Measuring face Ø	10 mm

Flatness of measuring faces	0.2 µm
Contact point travel	2.5 mm
Gauging force	7.5 N
Measuring range	50 - 100 mm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Calibration	L9
Type of product	Indicating snap gauge

## Services

Calibration Adjustable snap gauge Type RL	028730 RL
---	-----------