

FAHRION®
PRAZISION
Precision ER collet chuck CENTRO P, HSK-A 100 A = 160, Type CP for ER: 16

Order data

Order number	305960 16
GTIN	2050001703576
Item class	33F

Description
Version:

- **Ground externally and internally. With Balluffchip bore.**
- **Run-out and repetition accuracy 3 µm at 3×D, maximum 50 mm.**
- **Very high clamping forces due to the collet fully seated in the chuck and coated clamping nut.**
- **Vibration damping due to the element collet and mass of the chuck.**
- **Alternatively without seals, with ER clamping nut CP No. 309655 or sealed system with ER clamping nut CP for HP sealing rings No. 309665 in conjunction with HP sealing rings No.309666 – 309668 (for internal coolant supply or as a dirt trap!).**

Advantage:

Patented optimum seating of the collet, double guides, trapezoidal thread and low-friction coated clamping nut amalgamate when clamped into a sturdy unit, thus ensuring a very high degree of rigidity and precision.

Application:

For high precision clamping of tools with plain shanks.

Supplied with:

Without clamping nut and sealing rings.

Optional extras:

Precision ER collets for HP No. 309368 – 309381, and for taps No. 309402; 309419 (not Horex). ER clamping nuts CP No. 309655; 309665. HP sealing rings No. 309666 – 309668. CP roller bearing wrenches No. 309754; 309756.

Note:

- **CP chuck clamps only nominal Ø up to shank Ø tolerance h10.**
- **Use in combination with Fahrion collets.**

Machining strategy: HSC

Shape: A
 Clamping range: 1 - 10 mm
 External Ø D: 30 mm

Technical description

Clamping range	1 - 10 mm
Type CP for ER	16
External Ø D	30 mm
Shape	A
Series	Centro P
Adapter	HSK-A 100 A = 160
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity ER collet with CP collet chuck	≤ 6 µm
Concentricity HP collet with CP collet chuck	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

HP collet with seal Nominal clamping Ø d 8 mm	309371 8
HP collet Nominal clamping Ø d 6 mm	309370 6
HP collet Nominal clamping Ø d 2 mm	309370 2
HP collet Nominal clamping Ø d 1 mm	309370 1
CP sealing ring Clamping Ø (1 mm increments) 2 mm	309666 2
HP collet with seal Nominal clamping Ø d 4 mm	309371 4
ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309402 9
	309404 3,5

ER collet for machine taps with seal and spray nozzles
Nominal clamping Ø d 3,5 mm

HP collet with seal Nominal clamping Ø d 9 mm	309371 9
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309402 8
HP collet Nominal clamping Ø d 8 mm	309370 8
HP collet with seal and spray nozzles Nominal clamping Ø d 4 mm	309372 4
ER collet for machine taps with seal Nominal clamping Ø d 4 mm	309402 4
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309404 4,5
HP collet with seal Nominal clamping Ø d 5 mm	309371 5
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309402 4,5
HP collet set with seal (3; 4; 5; 6; 8; 10mm), 425 E	309391
HP collet Nominal clamping Ø d 3 mm	309370 3
ER collet for machine taps with seal Nominal clamping Ø d 2,8 mm	309402 2,8
HP collet with seal and spray nozzles Nominal clamping Ø d 8 mm	309372 8
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309404 7
CP roller bearing wrench Type 16	309754 16
ER collet for machine taps with seal Nominal clamping Ø d 3,5 mm	309402 3,5
HP collet with seal Nominal clamping Ø d 3 mm	309371 3
HP collet Nominal clamping Ø d 4 mm	309370 4
CP roller bearing wrench for torque wrenches Type 16	309756 16
CP sealing ring Clamping Ø (1 mm increments) 1 mm	309666 1
HP collet with seal Nominal clamping Ø d 7 mm	309371 7
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309402 6

HP collet with seal Nominal clamping Ø d 10 mm	309371 10
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309402 7
HP collet Nominal clamping Ø d 9 mm	309370 9
HP collet Nominal clamping Ø d 7 mm	309370 7
HP collet Nominal clamping Ø d 5 mm	309370 5
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309404 8
HP collet with seal and spray nozzles Nominal clamping Ø d 6 mm	309372 6
HP collet with seal Nominal clamping Ø d 6 mm	309371 6
HP collet Nominal clamping Ø d 10 mm	309370 10
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309404 6
HP collet set (3; 4; 5; 6; 8; 10mm), 426 E	309390