

Garant
Face mill arbor with cooling channel bore, HSK-A 63 short, Spigot \varnothing d1: 40mm

Order data

Order number	306530 40
GTIN	4045197656803
Item class	31A

Description
Version:

- **Clamping \varnothing 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With RFID/Balluffchip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, toggle spanner No. 309840, milling cutter lock screw for internal coolant supply No. 309861.

Technical description

Overhang dimension A	60 mm
Milling mandrel length L ₄	27 mm
Spare milling cutter lock screw No. 309860 / 309861	40
Suitable toggle spanner No. 309840	40
Spigot \varnothing d ₁	40 mm

External \varnothing D	88 mm
Clamping \varnothing D ₁	40 mm
Adapter	HSK-A 63 short
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel \varnothing 40 mm	309840 40
Milling cutter lock screw for mandrel \varnothing 40 mm	309860 40