

Garant
Face mill arbor, HSK-A 63 A = 160, Spigot Ø d1: 16 mm

Order data

Order number	306570 16
GTIN	4045197290243
Item class	31A

Description
Version:

- Spigot Ø 40 with 4 tapped holes for face mills to DIN 2079.
- With Balluffchip bore.
- Increased collar contact surface.
- HSK mating faces machined.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

External Ø D: 38 mm

Milling mandrel length L₄: 17 mm

Spare milling cutter lock screw No. 309860: 16

Technical description

Spare milling cutter lock screw No. 309860	16
Suitable toggle spanner No. 309840	16
Spigot Ø d ₁	16 mm
Milling mandrel length L ₄	17 mm

External Ø D	38 mm
Adapter	HSK-A 63 A = 160
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
Milling cutter lock screw for mandrel Ø 16 mm	309860 16