


## Garant

### Face mill arbor with cooling channel bore, HSK-F 63 A = 100, Spigot Ø d1: 16mm



#### Order data

Order number	306563 16
GTIN	4045197587855
Item class	31A

#### Description

##### Version:

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With cooling channel bores.

##### Application:

For clamping shell end mills and milling cutter heads.

##### Supplied with:

Lock screw

##### Optional extras:

Special toggle spanner No. 309840.

#### Technical description

Overhang dimension A	100 mm
Spare milling cutter lock screw No. 309860 / 309861	16
Spigot Ø d <sub>1</sub>	16 mm
Milling mandrel length L <sub>4</sub>	17 mm

Suitable toggle spanner No. 309840	16
External Ø D	38 mm
Clamping Ø D <sub>1</sub>	16 mm
Adapter	HSK-F 63 A = 100
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

---

## Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
Milling cutter lock screw for mandrel Ø 16 mm	309860 16