


Garant
Face mill arbor with cooling channel bore, HSK-F 63 A = 100, Spigot Ø d1: 32mm

Order data

Order number	306563 32
GTIN	4045197587886
Item class	31A

Description
Version:

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Special toggle spanner No. 309840.

Technical description

Milling mandrel length L ₄	24 mm
Spare milling cutter lock screw No. 309860 / 309861	32
Overhang dimension A	100 mm
Suitable toggle spanner No. 309840	32

Spigot $\varnothing d_1$	32 mm
External $\varnothing D$	78 mm
Clamping $\varnothing D_1$	32 mm
Adapter	HSK-F 63 A = 100
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Socket wrench for coolant tubes for HSK 32	309890 32
Toggle spanner for mandrel $\varnothing 32$ mm	309840 32
HSK coolant tube for HSK 32	309880 32
Milling cutter lock screw for mandrel $\varnothing 32$ mm	309860 32