



DS double-ended grinding machine, 400 V, Type: DS07/200



Order data

| | |
|--------------|-----------------|
| Order number | 077512 DS07/200 |
| GTIN | 2050001674180 |
| Item class | 03S |

Description

Version:

The **extremely smooth-running** motor ensures a long working life, even when run **continuously. Supplied without grinding wheels.**

Exceptionally robust three-phase double-ended bench grinding machines, bench-top type. Sturdy workpiece supports, restart inhibit, and eye protection shields ensure user safety.

Note:

Suitable grinding wheels can be found from No. 596100.

Technical description

| | |
|----------------------------|-------------------------|
| Power consumption | 500 W |
| Weight | 30 kg |
| maximum speed | 2900 min ⁻¹ |
| Manufacturer's designation | DS07/200 |
| Abrasive disc width T | 25 mm |
| Abrasive disc hole Ø H | 51 mm |
| Abrasive disc Ø D | 200 mm |
| Power supply | Mains operated |
| Type of product | Double grinding machine |

Accessories

| | |
|---|-------------|
| Bench grinding wheel D×T×H (mm) Type NK60 | 596400 NK60 |
| Bench grinding wheel D×T×H (mm) Type EK60 | 596350 EK60 |
| Bench grinding wheel D×T×H (mm) Type NK60 | 596220 NK60 |
| Bench grinding wheel D×T×H (mm) Type SC80 | 596350 SC80 |
| Bench grinding wheel D×T×H (mm) Type NK36 | 596350 NK36 |
| Bench grinding wheel D×T×H (mm) Type SC80 | 596220 SC80 |
| Bench grinding wheel D×T×H (mm) Type C800 | 596350 C800 |
| Bench grinding wheel D×T×H (mm) Type EK60 | 596220 EK60 |
| Bench grinding wheel D×T×H (mm) Type NK60 | 596350 NK60 |
| Bench grinding wheel D×T×H (mm) Type EK80 | 596400 EK80 |
| Bench grinding wheel D×T×H (mm) Type EK80 | 596350 EK80 |
| Bench grinding wheel D×T×H (mm) Type SC80 | 596400 SC80 |
| Tool mounting plate right-hand Type AT1 | 077525 AT1 |
| Tool mounting plate left-hand Type AT1 | 077519 AT1 |
| Bench grinding wheel D×T×H (mm) Type EK60 | 596400 EK60 |
| Support stand suitable for machine DS07 | 077513 DS07 |
| Bench grinding wheel D×T×H (mm) Type EK80 | 596220 EK80 |
| Eye protection shield for No. 077502 Type DS1 | 077509 DS1 |