

FAHRION®
FAHRENDEN PRESSION**ET collet for thread tapping, with axial compensation, ET 32, Nominal clamping \varnothing d: 11 mm****Order data**

Order number	309432 11
GTIN	2050001704139
Item class	34F

Description**Version:**

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 μ m.

Application:

For tapping on milling and turning centres.

Suitable for:

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Technical description

Nominal clamping \varnothing d	11 mm
Adapter	ET 32
Standard	Manufacturer's standard
Type	4538 E
External \varnothing D	33 mm
Overall length L	43 mm
Axial range	10 mm

Type of product

Collet