



## Clamping head smooth, SK 65, Clamping $\varnothing$ (0.5 mm increments): 4mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329930 4      |
| GTIN         | 2050001072474 |
| Item class   | 33H           |

### Description

#### Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

#### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|                        |        |
|------------------------|--------|
| Clamping $\varnothing$ | 4 mm   |
| Profile                | round  |
| Clamping face          | smooth |
| Hardness               | 60 HR  |
| Length L               | 58 mm  |

|                 |               |
|-----------------|---------------|
| Adapter         | SK 65         |
| Type of product | Clamping head |