

Garant
Face mill arbor, HSK-A 100 A = 160, Spigot Ø d1: 32mm

Order data

Order number	306690 32
GTIN	4045197290496
Item class	31A

Description
Version:

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Spigot Ø d ₁	32 mm
Spare milling cutter lock screw No. 309860 / 309861	32
Suitable toggle spanner No. 309840	32
Overhang dimension A	160 mm
Milling mandrel length L ₄	24 mm

External \varnothing D	78 mm
Clamping \varnothing D ₁	32 mm
Adapter	HSK-A 100 A = 160
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Socket wrench for coolant tubes for HSK 32	309890 32
HSK coolant tube for HSK 32	309880 32
Milling cutter lock screw for mandrel \varnothing 32 mm	309860 32
Toggle spanner for mandrel \varnothing 32 mm	309840 32