


FAHRION®
FAHRENDEN PROFISSUM
OZ collet for chuck, 4 # 32 mm, Nominal clamping \varnothing d: 14mm

Order data

Order number	309560 14
GTIN	2050001704733
Item class	39Y

Description
Version:

Spring steel, through hardened and ground. The through bore (longer clamping range than DIN collets) increases the clamping force. More slits than DIN collets, giving a greater insertion depth in the collet chuck. Suitable for jobber drills, for clamping on the guide land **Clamping range = Nominal size down to minus 0.5 mm.** 5 or 6 slits each end.

Advantage:

- **Better radial run-out = axially parallel centring in taper; no tumbling.**
- **Higher clamping force = due to improved grip.**
- **Higher system stiffness = suitable for high-speed milling.**
- **Longer tool life.**

Technical description

Nominal clamping \varnothing d	14 mm
for chuck	4 - 32 mm
Product name attribute	4 # 32 mm
Standard	ISO 10897
Type	467 E
External \varnothing D	43.7 mm

Overall length L	60 mm
Type of product	Collet