



High performance cutting compound, chlorine-free, Contents: 120g



Order data

Order number	084160 120
GTIN	2050000966033
Item class	08J

Description

Version:

Cutting compound for spot application. Straightforward application(dip or apply). Adheres to the cutting edge and only becomes liquid in use; very good lubrication properties, very high pressure stability.

Soft cutting compound.

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Application:

Multi-purpose compound for **tapping, reaming, milling, broaching, and sawing**.

Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys.

Technical description

Flashpoint	250 °C
Colour	brown

Spontaneous ignition temperature	320 °C
Version	Can
Shape	Paste
Storage temperature	5 - 40 °C
Contents	0.12 l
Type of product	Cutting oil / grinding oil