



## Top jaw set, 4 pieces, soft, for chuck type: 200 mm



### Order data

Order number	314500 200
GTIN	4019208035512
Item class	36R

### Description

#### Version:

**Precision milled** contact face, **not burnished**.

#### Application:

For fitting to hardened base jaws.

#### Material:

16 MnCr5

#### Suitable for :

**Four-jaw lathe chucks No. 312000; 312500; 312700.**

#### Note:

- **Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.**
- **Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.**

Aluminium top jaws **on request**.

suitable for colour code: Röhm geared scroll chucks and jaws

Length L: 87 mm

Height H: 43 mm

Slot width D: 7.96 mm

Bore spacing b: 44.45 mm

Tenon length A: 12.67 mm

### Technical description

Bore spacing b	44.45 mm
Slot width D	7.96 mm

Tenon length A	12.67 mm
Length L	87 mm
for chuck type	200 mm
Height H	43 mm
suitable for colour code	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chuck jaws