



## Micrometer with dial comparator, Measuring range: 25-50mm



### Order data

Order number	424800 25-50
GTIN	4059192004682
Item class	43A

### Description

#### Version:

Measuring spindle of stainless steel, hardened and ground. Carbide-tipped measuring faces. Controls and reading parts satin chrome-plated. With hand temperature protection. Constant measuring force. Moveable stop anvil, retractable. Particularly suitable for series manufactured parts.

#### Accuracy:

**Dial comparator DIN 863 – micrometer 2 µm.**

#### Supplied with:

Dial comparator Millimes No. 434674 size 50/1.

### Technical description

Measuring range	25 - 50 mm
Measuring range dial comparator	±0.05 mm
Barrel Ø	18 mm
Graduation of the precision dial comparator	0.001 mm
Spindle Ø	7.5 mm
Graduation of the micrometer	0.01 mm

Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B14
Type of product	Micrometer with dial comparator

### Services

CalibrationMicrometer with dial comparator maximum measuring range 100 mm	022400 100
DAkkS calibrationMicrometer with dial comparator maximum measuring range 100 mm	022410 100

### Accessories

Precision dial comparator $\pm$ measuring range / reading 50/1 $\mu$ m	434674 50/1
--	-------------