

FAHRION®
PRAZISION
ER clamping nut CENTRO P Standard, Type CP for ER: 16C

Order data

Order number	309655 16C
GTIN	2050001704849
Item class	34F

Description
Version:

Mini = all sizes with "M", extremely slim design.

MiniSlim = sizes with "MS", extremely super slim design.

Conical = all sizes with "C".

Standard = all other sizes.

With trapezoidal thread for high clamping forces. Extra long double guidance of the ER clamping nut. ER clamping nuts coated for reduction of **friction**.

ER clamping nut CP, **not suitable for HP sealing rings**.

Suitable for :

FAHRION ER collet chuck CENTRO P.

Optional extras:

Sealing rings No. 309666 – 309668. Clamping wrenches No. 309754 – 309756. HP collets No. 309349 – 309359.

Note:

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

Only the nominal size can be clamped (no intermediate range!)

Clamping range: 1 - 10 mm

Overall length L: 23.2 mm

External Ø D: 24 mm

maximum tightening torque: 55 N·m

Technical description

maximum tightening torque	55 N·m
Clamping range	1 - 10 mm
Overall length L	23.2 mm
External Ø D	24 mm
Series	Centro P
Type of product	Clamping nut

Accessories

Roller bearing wrench for torque wrench Type 16C	309756 16C
Roller bearing wrench Type 16C	309754 16C