

Garant**Centring vice, Jaw width A: 120mm****Order data**

Order number	360130 120
GTIN	4045197680891
Item class	310

Description**Version:**

Centring vice for flexible applications.

- **Absolute operational reliability thanks to enclosure.**
- **High repetition accuracy 0.02 mm.**
- **Variable central alignment ± 0.02 mm.**
- **Functional faces hardened.**
- **Sturdy design of tool steel, surface protection by brief exposure nitriding.**

Advantage:

Multi-functional uses.

- **Flexible lightweight.**

Application:

Ideal for 5-face machining, perfect for clamping blank parts.

Suitable for:

Multi-point clamping rails No. 360080 and 360110.

Supplied with:

Supplied with socket No. 642700 size E12.

Optional extras:

Types of jaws No. 360135– 360151.

Technical description

Weight	5.1 kg
Torque	60 Nm
Clamping force up to maximum	25.5 kN
Width	120 mm
Length	130 mm
Jaw width A	120 mm
Stroke	25 mm
Height	50.2 mm
suitable for colour code	ZC120
Type of product	Machine vice

Accessories

Centring/adapter plate Type T1	360132 T1
Pair of carbide top jaws for type 120	360136 120
Pair of gripp top jaws for type 120	360140 120
Pair of carbide top jaws for type 120	360135 120
Extension base for centring vice for type 120	360152 120
Pair of Vee jaws for type 120	360148 120
Clamping stud for centring vice Type 18M12/120	360131 18M12/120
Pair of carbide top jaws for type 120	360138 120
Pair of gripp top jaws for type 120	360143 120
Pair of soft top jaws for type 120	360145 120
Pair of gripp top jaws for type 120	360141 120
Clamping stud for centring vice Type 18M12/138	360131 18M12/138
Centring/adapter plate Type T2	360132 T2