

 Mahr**Digital caliper IP67 with rod type depth gauge, data output and ceramic measuring faces, Measuring range: 150mm****Order data**

Order number	412743 150
GTIN	4059192002282
Item class	43A

**Description****Version:**

Clearly legible, high-contrast LCD display. Inductive, waterproof measuring system. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. The measuring faces are precision-lapped.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032

**Optional extras:**

Data cable No. 498940.

**Technical description**

Jaw length	40 mm
Guidance	Raised slides
Calibration	A1
Depth gauge available	yes
Depth gauge	Ø 1.6
Auto switch-off	yes

Reversible reading	mm / inch
Standard	ISO 13385
Working time	approx. 3 years
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measuring range	0 - 150 mm
Measured value saving	MAHR reference-lock system
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.03$ mm
Interface	RS232C interface
Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

DAkKS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

## Accessories

Connection cablesimplex with data key Type USB2	498940 USB2
---	-------------

Button cell / special battery Battery type CR2032	081560 CR2032
Battery compartment cover	412235
Connection cablesimplex with data key Type D2	498940 D2
Connection cablesimplex with data key Type R2	498940 R2