


Garant**DN.G 150608, Grade: HU7305**

Order data

Order number	250762 HU7305
GTIN	4045197828903
Item class	21G

Description

DN.G 150608 HU7305 Grade: HU7305
Chip breaker: AM
Tolerance: G
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.1 - 0.6 mm/rev.
Cutting speed v_c main application: 400 - 600 m/min

Technical description

Grade	HU7305
Chip breaker	AM
Feed f	0.1 - 0.6 mm/rev.
Cutting speed v_c main application	400 - 600 m/min
Cutting depth a_p	0.5 - 5 mm
Main application	N
Corner radius	0.8 mm

Cutting conditions	slightly interrupted
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Tolerance	G
Type of product	Indexable insert for turning