



Workshop vernier caliper with parallax-free reading and fine adjustment, Measuring range: 300mm



Order data

Order number	415170 300
GTIN	4045197319012
Item class	41Z

Description

Version:

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened. Flat vernier scale for **parallax-free reading**, direct reading of **the internal dimensions** by means of additional scaling; with fine adjustment.

Technical description

Measuring range	0 - 300 mm
Calibration	A1
Jaw length	90 mm
Locking	Locking screw at top
Internal jaw Ø	10 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.08 mm
Fine setting	yes

Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Plastic case Type MS300	412470 MS300
-------------------------	--------------