

HOLEX**Workshop vernier caliper with parallax-free reading and fine adjustment,
Measuring range: 500mm****Order data**

Order number	415170 500
GTIN	4045197319029
Item class	41Z

Description**Version:**

Chamfered measuring tips for measurements to the root of threads and in narrow grooves. Offset and rounded jaw ends for internal measurements. High-contrast scale. With locking screw. Up to size 300 through hardened, from size 500 measuring faces hardened. Flat vernier scale for **parallax-free reading**, direct reading of **the internal dimensions** by means of additional scaling; with fine adjustment.

Technical description

Calibration	A1
Locking	Locking screw at top
Internal jaw \varnothing	20 mm
Jaw length	150 mm
Measuring range	0 - 500 mm
Graduation	1/20 mm
Packaging	sturdy box
Standard	ISO 13385
Measurement deviation E MPE	± 0.1 mm
Fine setting	yes

Measurement technology	analogue
Material	Stainless steel, INOX
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 500 mm	021000 500
DAkkS calibrationCalipers / depth gauges maximum measuring range 500 mm	021010 500