

STIEFELMAYER

Crankpin spirit level, Base Length×Width: 60X40mm**Order data**

Order number	469400 60X40
GTIN	4045197207241
Item class	46R

Description**Version:**

Sturdy housing of high quality special casting; hammer finish.
Longitudinal and traverse Vee profiles in the ground sole.
Longitudinal and traverse vials of glass.

Application:

Mainly used for aligning crankshafts and crankpins on engines.

Technical description

Sole width	40 mm
Reading transverse vial	0.8 mm/m
Sole length	60 mm
Reading longitudinal vial	0.1 mm/m
Standard	DIN 877
Packaging	sturdy box
Calibration	H2
Type of product	Spirit level

Services

Calibration Engineer's level / electronic clinometer
Accuracy 0,02 mm/m

026620 0,02