



Bench grinder ECO, 230 V, Type: W150



Order data

Order number	077502 W150
GTIN	2050001694607
Item class	03S

Description

Version:

Single-phase AC double-ended bench grinding machine with a **low-noise and maintenance-free motor**. **Generously-sized eye protection shields** ensure user safety. Workpiece rests can be **adjusted without tools**.

The **restart inhibit** prevents an unintentional start of the machine after a power failure.

Supplied with:

With regular aluminium oxide grinding wheels NK36 and NK60.

Note:

Suitable grinding wheels can be found under No. 596100 and No. 568733.

Suitable machine stand No. 077513 size DS04 with adapter plate No. 077515 size ECO.

Power consumption: 520 W

maximum speed: 2900 min⁻¹

Abrasive disc Ø D: 150 mm

Abrasive disc width T: 20 - 25 mm

Abrasive disc hole Ø H: 32 mm

Weight: 16 kg

Technical description

Weight	16 kg
Manufacturer's designation	W150

maximum speed	2900 min ⁻¹
Power consumption	520 W
Abrasive disc width T	20 - 25 mm
Abrasive disc hole Ø H	32 mm
Abrasive disc Ø D	150 mm
Power supply	Mains operated
Type of product	Double grinding machine

Accessories

Bench grinding wheel D×T×H (mm) Type EK80	596200 EK80
Bench grinding wheel D×T×H (mm) Type C800	596100 C800
Adaptor plate for ECO-DS04 suitable for ECO	077515 ECO
Bench grinding wheel D×T×H (mm) Type EK60	596200 EK60
Support stand suitable for machine DS04	077513 DS04
Bench grinding wheel D×T×H (mm) Type EK80	596100 EK80
Bench grinding wheel D×T×H (mm) Type C800	596200 C800
Bench grinding wheel D×T×H (mm) Type SC80	596100 SC80
Eye protection shield for No. 077502 Type ECO	077509 ECO
Bench grinding wheel D×T×H (mm) Type SC80	596200 SC80
Bench grinding wheel D×T×H (mm) Type NK60	596200 NK60